

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839908

Luminaire Tested: **LDS4C30D010 EU4309030 4LBPSMB**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309030 4LBPSMB
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2306.0 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839908

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839908

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49		
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44		
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148751
5°	148246
10°	146617
15°	144090
20°	140870
25°	137099
30°	132780
35°	127675
40°	121227
45°	110221
50°	90995
55°	66998
60°	45480
65°	26628
70°	10525
75°	2373
80°	3113
85°	5215



TEST NUMBER: P839908

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.9	4.9
10°-20°	319.0	13.8
20°-30°	465.3	20.2
30°-40°	531.1	23.0
40°-50°	482.9	20.9
50°-60°	284.8	12.3
60°-70°	95.5	4.1
70°-80°	10.0	0.4
80°-90°	3.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	898.2	39.0
0°-40°	1429.4	62.0
0°-60°	2197.0	95.3
0°-90°	2306.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2306.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1211	
5°	1202	114
15°	1133	319
25°	1011	465
35°	851	531
45°	634	483
55°	313	285
65°	92	96
75°	5	10
85°	4	3
90°	0	



TEST NUMBER: P839908

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1210.8
2.5°	1209.0
5°	1202.1
7.5°	1190.9
10°	1175.3
12.5°	1155.4
15°	1132.9
17.5°	1106.8
20°	1077.5
22.5°	1045.7
25°	1011.4
27.5°	974.0
30°	936.0
32.5°	894.3
35°	851.3
37.5°	804.5
40°	755.9
42.5°	699.2
45°	634.4
47.5°	559.6
50°	476.1
52.5°	392.6
55°	312.8
57.5°	244.9
60°	185.1
62.5°	134.0
65°	91.6
67.5°	56.1
70°	29.3
72.5°	11.2
75°	5.0
77.5°	5.0
80°	4.4
82.5°	3.7
85°	3.7
87.5°	3.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)