

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839624

Luminaire Tested: **LDS4C08D010 EU4089035 4LBSWH**

Issue Date: 8/24/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P839624  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C08D010 EU4089035 4LBSWH  
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBS TRIM WITH WH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 815.0 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839624

CATALOG NUMBER: LDS4C08D010 EU4089035 4LBSWH

### Luminous Intensity Polar Plot





TEST NUMBER: P839624

CATALOG NUMBER: LDS4C08D010 EU4089035 4LBSWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	52360
5°	52129
10°	51047
15°	49196
20°	46922
25°	44394
30°	41877
35°	39429
40°	37127
45°	34609
50°	31555
55°	27866
60°	23588
65°	18517
70°	13219
75°	7262
80°	1273
85°	0



TEST NUMBER: P839624

CATALOG NUMBER: LDS4C08D010 EU4089035 4LBSWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.9	4.9
10°-20°	108.5	13.3
20°-30°	150.7	18.5
30°-40°	164.5	20.2
40°-50°	153.4	18.8
50°-60°	116.5	14.3
60°-70°	63.7	7.8
70°-80°	17.6	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	299.1	36.7
0°-40°	463.6	56.9
0°-60°	733.5	90.0
0°-90°	815.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	426	
5°	423	40
15°	387	109
25°	328	151
35°	263	164
45°	199	153
55°	130	116
65°	64	64
75°	15	18
85°	0	0
90°	0	



TEST NUMBER: P839624

CATALOG NUMBER: LDS4C08D010 EU4089035 4LBSWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	426.2
2.5°	426.2
5°	422.7
7.5°	417.3
10°	409.2
12.5°	398.4
15°	386.8
17.5°	372.4
20°	358.9
22.5°	342.8
25°	327.5
27.5°	312.3
30°	295.2
32.5°	279.1
35°	262.9
37.5°	246.8
40°	231.5
42.5°	215.4
45°	199.2
47.5°	183.1
50°	165.1
52.5°	148.1
55°	130.1
57.5°	113.1
60°	96.0
62.5°	79.0
65°	63.7
67.5°	49.3
70°	36.8
72.5°	25.1
75°	15.3
77.5°	7.2
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)