

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839913

Luminaire Tested: **LDS4C30D010 EU4309030 4LBSLI**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309030 4LBSLI
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3010.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839913

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839913

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264037
5°	258065
10°	242337
15°	225465
20°	209102
25°	190616
30°	169706
35°	150426
40°	135195
45°	120993
50°	103801
55°	83512
60°	62213
65°	39709
70°	19145
75°	3180
80°	2335
85°	0



TEST NUMBER: P839913

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	6.5
10°-20°	497.0	16.5
20°-30°	644.0	21.4
30°-40°	631.1	21.0
40°-50°	534.9	17.8
50°-60°	350.6	11.6
60°-70°	140.9	4.7
70°-80°	16.1	0.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1335.9	44.4
0°-40°	1967.0	65.3
0°-60°	2852.5	94.8
0°-90°	3010.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3010.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2149	
5°	2093	195
15°	1773	497
25°	1406	644
35°	1003	631
45°	696	535
55°	390	351
65°	137	141
75°	7	16
85°	0	0
90°	0	



TEST NUMBER: P839913

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2149.2
2.5°	2132.6
5°	2092.6
7.5°	2025.9
10°	1942.6
12.5°	1852.7
15°	1772.7
17.5°	1686.1
20°	1599.4
22.5°	1506.2
25°	1406.2
27.5°	1302.8
30°	1196.3
32.5°	1096.3
35°	1003.0
37.5°	926.4
40°	843.0
42.5°	769.7
45°	696.4
47.5°	619.8
50°	543.1
52.5°	466.5
55°	389.9
57.5°	319.9
60°	253.2
62.5°	193.2
65°	136.6
67.5°	90.0
70°	53.3
72.5°	23.3
75°	6.7
77.5°	3.3
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)