

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839921

Luminaire Tested: **LDS4C30D010 EU4309035 4LBSGPH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309035 4LBSGPH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH GPH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1937.9 lumens
Efficiency: N/A
Efficacy: 61.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839921

CATALOG NUMBER: LDS4C30D010 EU4309035 4LBSGPH

Luminous Intensity Polar Plot





TEST NUMBER: P839921

CATALOG NUMBER: LDS4C30D010 EU4309035 4LBSGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125016
5°	124593
10°	123227
15°	121095
20°	118383
25°	115221
30°	111586
35°	107293
40°	101885
45°	92639
50°	76470
55°	56310
60°	38207
65°	22384
70°	8836
75°	1994
80°	2618
85°	4370



TEST NUMBER: P839921

CATALOG NUMBER: LDS4C30D010 EU4309035 4LBSGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.7	4.9
10°-20°	268.1	13.8
20°-30°	391.1	20.2
30°-40°	446.4	23.0
40°-50°	405.8	20.9
50°-60°	239.3	12.4
60°-70°	80.3	4.1
70°-80°	8.4	0.4
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.9	39.0
0°-40°	1201.3	62.0
0°-60°	1846.4	95.3
0°-90°	1937.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1937.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1018	
5°	1010	96
15°	952	268
25°	850	391
35°	715	446
45°	533	406
55°	263	239
65°	77	80
75°	4	8
85°	3	3
90°	0	



TEST NUMBER: P839921

CATALOG NUMBER: LDS4C30D010 EU4309035 4LBSGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1017.6
2.5°	1016.0
5°	1010.3
7.5°	1000.8
10°	987.8
12.5°	971.0
15°	952.1
17.5°	930.1
20°	905.5
22.5°	878.8
25°	850.0
27.5°	818.6
30°	786.6
32.5°	751.6
35°	715.4
37.5°	676.1
40°	635.3
42.5°	587.6
45°	533.2
47.5°	470.3
50°	400.1
52.5°	330.0
55°	262.9
57.5°	205.8
60°	155.5
62.5°	112.6
65°	77.0
67.5°	47.1
70°	24.6
72.5°	9.4
75°	4.2
77.5°	4.2
80°	3.7
82.5°	3.1
85°	3.1
87.5°	2.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)