

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839635

Luminaire Tested: **LDS4C08D010 EU4089040 4LBSWMH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089040 4LBSWMH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 4LBS TRIM WITH WMH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 779.0 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839635

CATALOG NUMBER: LDS4C08D010 EU4089040 4LBSWMH

Luminous Intensity Polar Plot





TEST NUMBER: P839635

CATALOG NUMBER: LDS4C08D010 EU4089040 4LBSWMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50051
5°	49822
10°	48789
15°	47021
20°	44856
25°	42442
30°	40033
35°	37689
40°	35491
45°	33080
50°	30160
55°	26645
60°	22556
65°	17703
70°	12644
75°	6930
80°	1203
85°	0



TEST NUMBER: P839635

CATALOG NUMBER: LDS4C08D010 EU4089040 4LBSWMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.2	4.9
10°-20°	103.7	13.3
20°-30°	144.0	18.5
30°-40°	157.2	20.2
40°-50°	146.6	18.8
50°-60°	111.3	14.3
60°-70°	61.0	7.8
70°-80°	16.8	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.9	36.7
0°-40°	443.1	56.9
0°-60°	701.1	90.0
0°-90°	779.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	779.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	407	
5°	404	38
15°	370	104
25°	313	144
35°	251	157
45°	190	147
55°	124	111
65°	61	61
75°	15	17
85°	0	0
90°	0	



TEST NUMBER: P839635

CATALOG NUMBER: LDS4C08D010 EU4089040 4LBSWMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	407.4
2.5°	407.4
5°	404.0
7.5°	398.9
10°	391.1
12.5°	380.8
15°	369.7
17.5°	356.0
20°	343.1
22.5°	327.6
25°	313.1
27.5°	298.5
30°	282.2
32.5°	266.7
35°	251.3
37.5°	235.9
40°	221.3
42.5°	205.8
45°	190.4
47.5°	175.0
50°	157.8
52.5°	141.5
55°	124.4
57.5°	108.1
60°	91.8
62.5°	75.5
65°	60.9
67.5°	47.2
70°	35.2
72.5°	24.0
75°	14.6
77.5°	6.9
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)