

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839636

Luminaire Tested: **LDS4C08D010 EU4089050 4LBCSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089050 4LBCSMB
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND
4LBCS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 630.0 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839636

CATALOG NUMBER: LDS4C08D010 EU4089050 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839636

CATALOG NUMBER: LDS4C08D010 EU4089050 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40640
5°	40499
10°	40057
15°	39364
20°	38489
25°	37454
30°	36273
35°	34885
40°	33117
45°	30109
50°	24866
55°	18313
60°	12433
65°	7267
70°	2874
75°	665
80°	849
85°	1410



TEST NUMBER: P839636

CATALOG NUMBER: LDS4C08D010 EU4089050 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.1	4.9
10°-20°	87.2	13.8
20°-30°	127.1	20.2
30°-40°	145.1	23.0
40°-50°	131.9	20.9
50°-60°	77.8	12.4
60°-70°	26.1	4.1
70°-80°	2.8	0.4
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.4	38.9
0°-40°	390.5	62.0
0°-60°	600.2	95.3
0°-90°	630.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	630.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	331	
5°	328	31
15°	310	87
25°	276	127
35°	233	145
45°	173	132
55°	86	78
65°	25	26
75°	1	3
85°	1	1
90°	0	



TEST NUMBER: P839636

CATALOG NUMBER: LDS4C08D010 EU4089050 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	330.8
2.5°	330.3
5°	328.4
7.5°	325.4
10°	321.1
12.5°	315.6
15°	309.5
17.5°	302.4
20°	294.4
22.5°	285.7
25°	276.3
27.5°	266.1
30°	255.7
32.5°	244.3
35°	232.6
37.5°	219.8
40°	206.5
42.5°	191.0
45°	173.3
47.5°	152.9
50°	130.1
52.5°	107.3
55°	85.5
57.5°	66.9
60°	50.6
62.5°	36.6
65°	25.0
67.5°	15.3
70°	8.0
72.5°	3.1
75°	1.4
77.5°	1.4
80°	1.2
82.5°	1.0
85°	1.0
87.5°	0.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)