

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839930

Luminaire Tested: **LDS4C30D010 EU4309040 4LBSB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309040 4LBSB
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH B FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1611.0 lumens
Efficiency: N/A
Efficacy: 51.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839930

CATALOG NUMBER: LDS4C30D010 EU4309040 4LBSB

Luminous Intensity Polar Plot





TEST NUMBER: P839930

CATALOG NUMBER: LDS4C30D010 EU4309040 4LBSB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103922
5°	103566
10°	102431
15°	100669
20°	98406
25°	95782
30°	92762
35°	89191
40°	84693
45°	77002
50°	63569
55°	46822
60°	31770
65°	18605
70°	7364
75°	1661
80°	2122
85°	3665



TEST NUMBER: P839930

CATALOG NUMBER: LDS4C30D010 EU4309040 4LBSB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.6	4.9
10°-20°	222.9	13.8
20°-30°	325.1	20.2
30°-40°	371.1	23.0
40°-50°	337.3	20.9
50°-60°	199.0	12.4
60°-70°	66.7	4.1
70°-80°	7.0	0.4
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	627.5	39.0
0°-40°	998.6	62.0
0°-60°	1534.9	95.3
0°-90°	1611.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1611.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	846	
5°	840	80
15°	792	223
25°	707	325
35°	595	371
45°	443	337
55°	219	199
65°	64	67
75°	4	7
85°	3	2
90°	0	



TEST NUMBER: P839930

CATALOG NUMBER: LDS4C30D010 EU4309040 4LBSB

CANDELA DISTRIBUTION (FULL):

	0°
0°	845.9
2.5°	844.6
5°	839.8
7.5°	832.0
10°	821.1
12.5°	807.2
15°	791.5
17.5°	773.2
20°	752.7
22.5°	730.5
25°	706.6
27.5°	680.5
30°	653.9
32.5°	624.7
35°	594.7
37.5°	562.1
40°	528.1
42.5°	488.5
45°	443.2
47.5°	391.0
50°	332.6
52.5°	274.3
55°	218.6
57.5°	171.1
60°	129.3
62.5°	93.6
65°	64.0
67.5°	39.2
70°	20.5
72.5°	7.8
75°	3.5
77.5°	3.5
80°	3.0
82.5°	2.6
85°	2.6
87.5°	2.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)