

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839934

Luminaire Tested: **LDS4C30D010 EU4309040 4LBSWH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309040 4LBSWH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH WH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2726.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839934

CATALOG NUMBER: LDS4C30D010 EU4309040 4LBSWH

Luminous Intensity Polar Plot





TEST NUMBER: P839934

CATALOG NUMBER: LDS4C30D010 EU4309040 4LBSWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	175152
5°	174341
10°	170744
15°	164529
20°	156964
25°	148499
30°	140086
35°	131889
40°	124193
45°	115764
50°	105559
55°	93215
60°	78921
65°	61947
70°	44217
75°	24208
80°	4245
85°	0



TEST NUMBER: P839934

CATALOG NUMBER: LDS4C30D010 EU4309040 4LBSWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.5	4.9
10°-20°	363.0	13.3
20°-30°	504.1	18.5
30°-40°	550.1	20.2
40°-50°	513.1	18.8
50°-60°	389.5	14.3
60°-70°	213.3	7.8
70°-80°	58.7	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1000.6	36.7
0°-40°	1550.6	56.9
0°-60°	2453.2	90.0
0°-90°	2726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2726.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1426	
5°	1414	134
15°	1294	363
25°	1096	504
35°	879	550
45°	666	513
55°	435	389
65°	213	213
75°	51	59
85°	0	1
90°	0	



TEST NUMBER: P839934

CATALOG NUMBER: LDS4C30D010 EU4309040 4LBSWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1425.7
2.5°	1425.7
5°	1413.7
7.5°	1395.7
10°	1368.7
12.5°	1332.7
15°	1293.6
17.5°	1245.6
20°	1200.6
22.5°	1146.5
25°	1095.5
27.5°	1044.5
30°	987.5
32.5°	933.4
35°	879.4
37.5°	825.4
40°	774.4
42.5°	720.3
45°	666.3
47.5°	612.3
50°	552.3
52.5°	495.2
55°	435.2
57.5°	378.2
60°	321.2
62.5°	264.2
65°	213.1
67.5°	165.1
70°	123.1
72.5°	84.1
75°	51.0
77.5°	24.0
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)