

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839638

Luminaire Tested: **LDS4C08D010 EU4089050 4LBPSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839638
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089050 4LBPSMB
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 715.0 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839638

CATALOG NUMBER: LDS4C08D010 EU4089050 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839638

CATALOG NUMBER: LDS4C08D010 EU4089050 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46119
5°	45962
10°	45458
15°	44681
20°	43680
25°	42510
30°	41167
35°	39579
40°	37592
45°	34175
50°	28210
55°	20776
60°	14104
65°	8256
70°	3269
75°	712
80°	990
85°	1692



TEST NUMBER: P839638

CATALOG NUMBER: LDS4C08D010 EU4089050 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.3	4.9
10°-20°	98.9	13.8
20°-30°	144.3	20.2
30°-40°	164.7	23.0
40°-50°	149.7	20.9
50°-60°	88.3	12.3
60°-70°	29.6	4.1
70°-80°	3.1	0.4
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.5	39.0
0°-40°	443.2	62.0
0°-60°	681.2	95.3
0°-90°	715.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	715.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	375	
5°	373	35
15°	351	99
25°	314	144
35°	264	165
45°	197	150
55°	97	88
65°	28	30
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P839638

CATALOG NUMBER: LDS4C08D010 EU4089050 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	375.4
2.5°	374.9
5°	372.7
7.5°	369.3
10°	364.4
12.5°	358.2
15°	351.3
17.5°	343.2
20°	334.1
22.5°	324.2
25°	313.6
27.5°	302.0
30°	290.2
32.5°	277.3
35°	263.9
37.5°	249.5
40°	234.4
42.5°	216.8
45°	196.7
47.5°	173.5
50°	147.6
52.5°	121.7
55°	97.0
57.5°	75.9
60°	57.4
62.5°	41.5
65°	28.4
67.5°	17.4
70°	9.1
72.5°	3.5
75°	1.5
77.5°	1.5
80°	1.4
82.5°	1.2
85°	1.2
87.5°	1.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)