

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839665

Luminaire Tested: **LDS4C100D010 EU41009030 4LBSWMH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C100D010 EU41009030 4LBSWMH
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH WMH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8838.0 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839665

CATALOG NUMBER: LDS4C100D010 EU41009030 4LBSWMH

Luminous Intensity Polar Plot





TEST NUMBER: P839665

CATALOG NUMBER: LDS4C100D010 EU41009030 4LBSWMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77				77
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				67
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58				58
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51				51
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34				34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	567853
5°	565225
10°	553560
15°	533436
20°	508884
25°	481460
30°	454162
35°	427613
40°	402618
45°	375315
50°	342230
55°	302241
60°	255830
65°	200842
70°	143357
75°	78558
80°	13867
85°	0



TEST NUMBER: P839665

CATALOG NUMBER: LDS4C100D010 EU41009030 4LBSWMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	433.0	4.9
10°-20°	1176.8	13.3
20°-30°	1634.3	18.5
30°-40°	1783.4	20.2
40°-50°	1663.6	18.8
50°-60°	1262.7	14.3
60°-70°	691.4	7.8
70°-80°	190.3	2.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3244.0	36.7
0°-40°	5027.4	56.9
0°-60°	7953.7	90.0
0°-90°	8838.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8838.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4622	
5°	4583	433
15°	4194	1177
25°	3552	1634
35°	2851	1783
45°	2160	1664
55°	1411	1263
65°	691	691
75°	166	190
85°	0	3
90°	0	



TEST NUMBER: P839665

CATALOG NUMBER: LDS4C100D010 EU41009030 4LBSWMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4622.2
2.5°	4622.2
5°	4583.3
7.5°	4525.1
10°	4437.4
12.5°	4320.7
15°	4194.1
17.5°	4038.5
20°	3892.4
22.5°	3717.2
25°	3551.8
27.5°	3386.5
30°	3201.5
32.5°	3026.3
35°	2851.2
37.5°	2676.0
40°	2510.5
42.5°	2335.4
45°	2160.2
47.5°	1985.1
50°	1790.6
52.5°	1605.6
55°	1411.1
57.5°	1226.0
60°	1041.2
62.5°	856.4
65°	690.9
67.5°	535.1
70°	399.1
72.5°	272.5
75°	165.5
77.5°	77.8
80°	19.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)