

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839667

Luminaire Tested: **LDS4C100D010 EU41009035 4LBCSMMS**

Issue Date: 8/24/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P839667  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C100D010 EU41009035 4LBCSMMS  
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBCS TRIM WITH MMS FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7261.0 lumens  
Efficiency: N/A  
Efficacy: 63.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 114.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839667

CATALOG NUMBER: LDS4C100D010 EU41009035 4LBCSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P839667

CATALOG NUMBER: LDS4C100D010 EU41009035 4LBCSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	468391
5°	466789
10°	461670
15°	453715
20°	443555
25°	431698
30°	418101
35°	401997
40°	381722
45°	347065
50°	286517
55°	210976
60°	143198
65°	83837
70°	33118
75°	7452
80°	9693
85°	16633



TEST NUMBER: P839667

CATALOG NUMBER: LDS4C100D010 EU41009035 4LBCSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	358.6	4.9
10°-20°	1004.5	13.8
20°-30°	1465.2	20.2
30°-40°	1672.4	23.0
40°-50°	1520.4	20.9
50°-60°	896.7	12.3
60°-70°	300.7	4.1
70°-80°	31.4	0.4
80°-90°	11.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2828.3	39.0
0°-40°	4500.7	62.0
0°-60°	6917.9	95.3
0°-90°	7261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7261.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3813	
5°	3785	359
15°	3567	1004
25°	3185	1465
35°	2680	1672
45°	1998	1520
55°	985	897
65°	288	301
75°	16	31
85°	12	11
90°	0	



TEST NUMBER: P839667

CATALOG NUMBER: LDS4C100D010 EU41009035 4LBCSMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3812.6
2.5°	3806.7
5°	3785.1
7.5°	3749.8
10°	3700.8
12.5°	3638.0
15°	3567.3
17.5°	3484.9
20°	3392.7
22.5°	3292.6
25°	3184.7
27.5°	3067.0
30°	2947.3
32.5°	2815.8
35°	2680.4
37.5°	2533.2
40°	2380.2
42.5°	2201.6
45°	1997.6
47.5°	1762.1
50°	1499.1
52.5°	1236.2
55°	985.0
57.5°	771.2
60°	582.8
62.5°	421.9
65°	288.4
67.5°	176.6
70°	92.2
72.5°	35.3
75°	15.7
77.5°	15.7
80°	13.7
82.5°	11.8
85°	11.8
87.5°	9.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)