

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839952

Luminaire Tested: **LDS4C35D010 EU4359027 4LBSH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359027 4LBSH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3276.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839952

CATALOG NUMBER: LDS4C35D010 EU4359027 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839952

CATALOG NUMBER: LDS4C35D010 EU4359027 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210485
5°	209513
10°	205187
15°	197725
20°	188629
25°	178457
30°	168344
35°	158495
40°	149244
45°	139114
50°	126850
55°	112021
60°	94843
65°	74447
70°	53126
75°	29097
80°	5165
85°	0



TEST NUMBER: P839952

CATALOG NUMBER: LDS4C35D010 EU4359027 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.5	4.9
10°-20°	436.2	13.3
20°-30°	605.8	18.5
30°-40°	661.0	20.2
40°-50°	616.6	18.8
50°-60°	468.0	14.3
60°-70°	256.3	7.8
70°-80°	70.5	2.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1202.5	36.7
0°-40°	1863.5	56.9
0°-60°	2948.2	90.0
0°-90°	3276.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3276.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1713	
5°	1699	160
15°	1555	436
25°	1316	606
35°	1057	661
45°	801	617
55°	523	468
65°	256	256
75°	61	71
85°	0	1
90°	0	



TEST NUMBER: P839952

CATALOG NUMBER: LDS4C35D010 EU4359027 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1713.3
2.5°	1713.3
5°	1698.9
7.5°	1677.3
10°	1644.8
12.5°	1601.6
15°	1554.6
17.5°	1497.0
20°	1442.8
22.5°	1377.9
25°	1316.5
27.5°	1255.3
30°	1186.7
32.5°	1121.8
35°	1056.8
37.5°	991.9
40°	930.6
42.5°	865.7
45°	800.7
47.5°	735.8
50°	663.7
52.5°	595.1
55°	523.0
57.5°	454.5
60°	386.0
62.5°	317.4
65°	256.1
67.5°	198.4
70°	147.9
72.5°	101.0
75°	61.3
77.5°	28.8
80°	7.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)