

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839969

Luminaire Tested: **LDS4C35D010 EU4359035 4LBPSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359035 4LBPSMMS
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2822.0 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839969

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839969

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																											
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																											
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70																											
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62																											
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55																											
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49																											
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																											
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																											
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36																											
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182044
5°	181420
10°	179426
15°	176345
20°	172391
25°	167775
30°	162499
35°	156230
40°	148362
45°	134893
50°	111350
55°	81991
60°	55653
65°	32587
70°	12859
75°	2895
80°	3750
85°	6484



TEST NUMBER: P839969

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	4.9
10°-20°	390.4	13.8
20°-30°	569.4	20.2
30°-40°	650.0	23.0
40°-50°	590.9	20.9
50°-60°	348.5	12.3
60°-70°	116.9	4.1
70°-80°	12.2	0.4
80°-90°	4.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1099.2	39.0
0°-40°	1749.2	62.0
0°-60°	2688.7	95.3
0°-90°	2822.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2822.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1482	
5°	1471	139
15°	1386	390
25°	1238	569
35°	1042	650
45°	776	591
55°	383	349
65°	112	117
75°	6	12
85°	5	4
90°	0	



TEST NUMBER: P839969

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1481.8
2.5°	1479.5
5°	1471.1
7.5°	1457.4
10°	1438.3
12.5°	1413.9
15°	1386.5
17.5°	1354.4
20°	1318.6
22.5°	1279.7
25°	1237.7
27.5°	1192.0
30°	1145.5
32.5°	1094.4
35°	1041.7
37.5°	984.5
40°	925.1
42.5°	855.7
45°	776.4
47.5°	684.8
50°	582.6
52.5°	480.5
55°	382.8
57.5°	299.7
60°	226.5
62.5°	164.0
65°	112.1
67.5°	68.6
70°	35.8
72.5°	13.7
75°	6.1
77.5°	6.1
80°	5.3
82.5°	4.6
85°	4.6
87.5°	3.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)