

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839676

Luminaire Tested: **LDS4C100D010 EU41009040 4LBCSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839676
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C100D010 EU41009040 4LBCSMB
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBCS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7112.0 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839676

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839676

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	458784
5°	457219
10°	452189
15°	444405
20°	434455
25°	422847
30°	409518
35°	393748
40°	373879
45°	339942
50°	280650
55°	206649
60°	140250
65°	82122
70°	32436
75°	7310
80°	9551
85°	16210



TEST NUMBER: P839676

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	351.3	4.9
10°-20°	983.9	13.8
20°-30°	1435.1	20.2
30°-40°	1638.1	23.0
40°-50°	1489.2	20.9
50°-60°	878.3	12.3
60°-70°	294.6	4.1
70°-80°	30.8	0.4
80°-90°	10.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2770.3	39.0
0°-40°	4408.4	62.0
0°-60°	6775.9	95.3
0°-90°	7112.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7112.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3734	
5°	3708	351
15°	3494	984
25°	3119	1435
35°	2625	1638
45°	1957	1489
55°	965	878
65°	282	295
75°	15	31
85°	12	11
90°	0	



TEST NUMBER: P839676

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3734.4
2.5°	3728.6
5°	3707.5
7.5°	3672.9
10°	3624.8
12.5°	3563.3
15°	3494.1
17.5°	3413.4
20°	3323.1
22.5°	3225.1
25°	3119.4
27.5°	3004.0
30°	2886.8
32.5°	2758.0
35°	2625.4
37.5°	2481.3
40°	2331.3
42.5°	2156.4
45°	1956.6
47.5°	1725.9
50°	1468.4
52.5°	1210.8
55°	964.8
57.5°	755.3
60°	570.8
62.5°	413.2
65°	282.5
67.5°	173.0
70°	90.3
72.5°	34.6
75°	15.4
77.5°	15.4
80°	13.5
82.5°	11.5
85°	11.5
87.5°	9.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)