

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839972

Luminaire Tested: **LDS4C35D010 EU4359035 4LBSH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359035 4LBSH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3454.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839972

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839972

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	221923
5°	220896
10°	216339
15°	208473
20°	198879
25°	188162
30°	177494
35°	167119
40°	157343
45°	146672
50°	133750
55°	118125
60°	99978
65°	78488
70°	56035
75°	30711
80°	5377
85°	0



TEST NUMBER: P839972

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.2	4.9
10°-20°	459.9	13.3
20°-30°	638.7	18.5
30°-40°	697.0	20.2
40°-50°	650.1	18.8
50°-60°	493.5	14.3
60°-70°	270.2	7.8
70°-80°	74.4	2.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1267.8	36.7
0°-40°	1964.8	56.9
0°-60°	3108.4	90.0
0°-90°	3454.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3454.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1806	
5°	1791	169
15°	1639	460
25°	1388	639
35°	1114	697
45°	844	650
55°	552	494
65°	270	270
75°	65	74
85°	0	1
90°	0	



TEST NUMBER: P839972

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1806.4
2.5°	1806.4
5°	1791.2
7.5°	1768.5
10°	1734.2
12.5°	1688.6
15°	1639.1
17.5°	1578.3
20°	1521.2
22.5°	1452.7
25°	1388.1
27.5°	1323.5
30°	1251.2
32.5°	1182.7
35°	1114.3
37.5°	1045.8
40°	981.1
42.5°	912.7
45°	844.2
47.5°	775.8
50°	699.8
52.5°	627.5
55°	551.5
57.5°	479.2
60°	406.9
62.5°	334.7
65°	270.0
67.5°	209.1
70°	156.0
72.5°	106.5
75°	64.7
77.5°	30.4
80°	7.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)