

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839977

Luminaire Tested: **LDS4C35D010 EU4359040 4LBCSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359040 4LBCSMMS
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBCS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2488.0 lumens
Efficiency: N/A
Efficacy: 61.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839977

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839977

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160496
5°	159950
10°	158194
15°	155474
20°	151983
25°	147916
30°	143263
35°	137738
40°	130801
45°	118926
50°	98181
55°	72289
60°	49068
65°	28721
70°	11351
75°	2563
80°	3325
85°	5638



TEST NUMBER: P839977

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.9	4.9
10°-20°	344.2	13.8
20°-30°	502.0	20.2
30°-40°	573.0	23.0
40°-50°	521.0	20.9
50°-60°	307.3	12.3
60°-70°	103.0	4.1
70°-80°	10.8	0.4
80°-90°	3.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.1	39.0
0°-40°	1542.2	62.0
0°-60°	2370.4	95.3
0°-90°	2488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1306	
5°	1297	123
15°	1222	344
25°	1091	502
35°	918	573
45°	684	521
55°	338	307
65°	99	103
75°	5	11
85°	4	4
90°	0	



TEST NUMBER: P839977

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1306.4
2.5°	1304.4
5°	1297.0
7.5°	1284.9
10°	1268.1
12.5°	1246.6
15°	1222.4
17.5°	1194.1
20°	1162.5
22.5°	1128.2
25°	1091.2
27.5°	1050.9
30°	1009.9
32.5°	964.8
35°	918.4
37.5°	868.0
40°	815.6
42.5°	754.4
45°	684.5
47.5°	603.8
50°	513.7
52.5°	423.6
55°	337.5
57.5°	264.2
60°	199.7
62.5°	144.6
65°	98.8
67.5°	60.5
70°	31.6
72.5°	12.1
75°	5.4
77.5°	5.4
80°	4.7
82.5°	4.0
85°	4.0
87.5°	3.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)