

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839684

Luminaire Tested: **LDS4C100D010 EU41009040 4LBSWH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C100D010 EU41009040 4LBSWH
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH WH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9403.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839684

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBSWH

Luminous Intensity Polar Plot





TEST NUMBER: P839684

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBSWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	604157
5°	601359
10°	588951
15°	567535
20°	541412
25°	512231
30°	483186
35°	454938
40°	428358
45°	399309
50°	364114
55°	321561
60°	272194
65°	213691
70°	152516
75°	83589
80°	14716
85°	0



TEST NUMBER: P839684

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBSWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	460.6	4.9
10°-20°	1252.0	13.3
20°-30°	1738.7	18.5
30°-40°	1897.4	20.2
40°-50°	1769.9	18.8
50°-60°	1343.4	14.3
60°-70°	735.6	7.8
70°-80°	202.5	2.2
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3451.4	36.7
0°-40°	5348.7	56.9
0°-60°	8462.1	90.0
0°-90°	9403.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9403.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4918	
5°	4876	461
15°	4462	1252
25°	3779	1739
35°	3033	1897
45°	2298	1770
55°	1501	1343
65°	735	736
75°	176	202
85°	0	3
90°	0	



TEST NUMBER: P839684

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBSWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4917.7
2.5°	4917.7
5°	4876.3
7.5°	4814.4
10°	4721.1
12.5°	4596.9
15°	4462.2
17.5°	4296.7
20°	4141.2
22.5°	3954.9
25°	3778.8
27.5°	3603.0
30°	3406.1
32.5°	3219.8
35°	3033.4
37.5°	2847.1
40°	2671.0
42.5°	2484.7
45°	2298.3
47.5°	2112.0
50°	1905.1
52.5°	1708.2
55°	1501.3
57.5°	1304.4
60°	1107.8
62.5°	911.2
65°	735.1
67.5°	569.3
70°	424.6
72.5°	289.9
75°	176.1
77.5°	82.8
80°	20.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)