

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839980

Luminaire Tested: **LDS4C35D010 EU4359040 4LBSB**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839980  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C35D010 EU4359040 4LBSB  
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 4LBS TRIM WITH B FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1901.0 lumens  
Efficiency: N/A  
Efficacy: 47.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839980

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBSB

### Luminous Intensity Polar Plot





TEST NUMBER: P839980

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBSB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	122632
5°	122213
10°	120869
15°	118793
20°	116121
25°	113025
30°	109458
35°	105253
40°	99945
45°	90867
50°	75017
55°	55239
60°	37495
65°	21948
70°	8657
75°	1946
80°	2547
85°	4370



TEST NUMBER: P839980

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBSB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.9	4.9
10°-20°	263.0	13.8
20°-30°	383.6	20.2
30°-40°	437.9	23.0
40°-50°	398.1	20.9
50°-60°	234.8	12.4
60°-70°	78.7	4.1
70°-80°	8.2	0.4
80°-90°	2.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.5	39.0
0°-40°	1178.3	62.0
0°-60°	1811.2	95.3
0°-90°	1901.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1901.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	998	
5°	991	94
15°	934	263
25°	834	384
35°	702	438
45°	523	398
55°	258	235
65°	76	79
75°	4	8
85°	3	3
90°	0	



TEST NUMBER: P839980

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBSB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	998.2
2.5°	996.6
5°	991.0
7.5°	981.7
10°	968.9
12.5°	952.5
15°	934.0
17.5°	912.4
20°	888.2
22.5°	862.0
25°	833.8
27.5°	803.0
30°	771.6
32.5°	737.2
35°	701.8
37.5°	663.2
40°	623.2
42.5°	576.4
45°	523.0
47.5°	461.3
50°	392.5
52.5°	323.7
55°	257.9
57.5°	201.9
60°	152.6
62.5°	110.5
65°	75.5
67.5°	46.2
70°	24.1
72.5°	9.2
75°	4.1
77.5°	4.1
80°	3.6
82.5°	3.1
85°	3.1
87.5°	2.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)