

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839695

Luminaire Tested: **LDS4C100D010 EU41009050 4LBSWMH**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839695  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C100D010 EU41009050 4LBSWMH  
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBS TRIM WITH WMH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9160.0 lumens  
Efficiency: N/A  
Efficacy: 80.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 114.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839695

CATALOG NUMBER: LDS4C100D010 EU41009050 4LBSWMH

### Luminous Intensity Polar Plot





TEST NUMBER: P839695

CATALOG NUMBER: LDS4C100D010 EU41009050 4LBSWMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	588542
5°	585820
10°	573732
15°	552870
20°	527423
25°	499001
30°	470702
35°	443180
40°	417293
45°	388989
50°	354692
55°	313251
60°	265167
65°	208167
70°	148565
75°	81406
80°	14362
85°	0



TEST NUMBER: P839695

CATALOG NUMBER: LDS4C100D010 EU41009050 4LBSWMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	448.7	4.9
10°-20°	1219.7	13.3
20°-30°	1693.8	18.5
30°-40°	1848.3	20.2
40°-50°	1724.2	18.8
50°-60°	1308.7	14.3
60°-70°	716.6	7.8
70°-80°	197.2	2.2
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3362.2	36.7
0°-40°	5210.5	56.9
0°-60°	8243.4	90.0
0°-90°	9160.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9160.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4791	
5°	4750	449
15°	4347	1220
25°	3681	1694
35°	2955	1848
45°	2239	1724
55°	1462	1309
65°	716	717
75°	172	197
85°	0	3
90°	0	



TEST NUMBER: P839695

CATALOG NUMBER: LDS4C100D010 EU41009050 4LBSWMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4790.6
2.5°	4790.6
5°	4750.3
7.5°	4689.9
10°	4599.1
12.5°	4478.1
15°	4346.9
17.5°	4185.7
20°	4034.2
22.5°	3852.7
25°	3681.2
27.5°	3509.9
30°	3318.1
32.5°	3136.6
35°	2955.0
37.5°	2773.5
40°	2602.0
42.5°	2420.5
45°	2238.9
47.5°	2057.4
50°	1855.8
52.5°	1664.1
55°	1462.5
57.5°	1270.7
60°	1079.2
62.5°	887.6
65°	716.1
67.5°	554.6
70°	413.6
72.5°	282.4
75°	171.5
77.5°	80.6
80°	20.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)