

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839984

Luminaire Tested: **LDS4C35D010 EU4359040 4LBSWH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359040 4LBSWH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH WH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3217.0 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839984

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBSWH

Luminous Intensity Polar Plot





TEST NUMBER: P839984

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBSWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206701
5°	205739
10°	201494
15°	194164
20°	185230
25°	175244
30°	165308
35°	155646
40°	146550
45°	136613
50°	124576
55°	110007
60°	93123
65°	73110
70°	52192
75°	28575
80°	5023
85°	0



TEST NUMBER: P839984

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBSWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	4.9
10°-20°	428.3	13.3
20°-30°	594.9	18.5
30°-40°	649.1	20.2
40°-50°	605.6	18.8
50°-60°	459.6	14.3
60°-70°	251.7	7.8
70°-80°	69.3	2.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1180.8	36.7
0°-40°	1829.9	56.9
0°-60°	2895.1	90.0
0°-90°	3217.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3217.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1682	
5°	1668	158
15°	1527	428
25°	1293	595
35°	1038	649
45°	786	606
55°	514	460
65°	252	252
75°	60	69
85°	0	1
90°	0	



TEST NUMBER: P839984

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBSWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1682.5
2.5°	1682.5
5°	1668.3
7.5°	1647.1
10°	1615.2
12.5°	1572.7
15°	1526.6
17.5°	1470.0
20°	1416.8
22.5°	1353.1
25°	1292.8
27.5°	1232.7
30°	1165.3
32.5°	1101.6
35°	1037.8
37.5°	974.1
40°	913.8
42.5°	850.1
45°	786.3
47.5°	722.6
50°	651.8
52.5°	584.4
55°	513.6
57.5°	446.3
60°	379.0
62.5°	311.7
65°	251.5
67.5°	194.8
70°	145.3
72.5°	99.2
75°	60.2
77.5°	28.3
80°	7.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)