

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839992

Luminaire Tested: **LDS4C35D010 EU4359050 4LBSH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359050 4LBSH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3530.0 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839992

CATALOG NUMBER: LDS4C35D010 EU4359050 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839992

CATALOG NUMBER: LDS4C35D010 EU4359050 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226812
5°	225755
10°	221092
15°	213064
20°	203258
25°	192297
30°	181395
35°	170793
40°	160807
45°	149904
50°	136693
55°	120717
60°	102190
65°	80232
70°	57256
75°	31376
80°	5518
85°	0



TEST NUMBER: P839992

CATALOG NUMBER: LDS4C35D010 EU4359050 4LSBH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.9	4.9
10°-20°	470.0	13.3
20°-30°	652.7	18.5
30°-40°	712.3	20.2
40°-50°	664.5	18.8
50°-60°	504.4	14.3
60°-70°	276.2	7.8
70°-80°	76.0	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1295.7	36.7
0°-40°	2008.0	56.9
0°-60°	3176.8	90.0
0°-90°	3530.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3530.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1846	
5°	1831	173
15°	1675	470
25°	1419	653
35°	1139	712
45°	863	664
55°	564	504
65°	276	276
75°	66	76
85°	0	1
90°	0	



TEST NUMBER: P839992

CATALOG NUMBER: LDS4C35D010 EU4359050 4LBSH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1846.2
2.5°	1846.2
5°	1830.6
7.5°	1807.4
10°	1772.3
12.5°	1725.7
15°	1675.2
17.5°	1613.0
20°	1554.7
22.5°	1484.7
25°	1418.6
27.5°	1352.6
30°	1278.7
32.5°	1208.7
35°	1138.8
37.5°	1068.8
40°	1002.7
42.5°	932.8
45°	862.8
47.5°	792.9
50°	715.2
52.5°	641.3
55°	563.6
57.5°	489.7
60°	415.9
62.5°	342.1
65°	276.0
67.5°	213.7
70°	159.4
72.5°	108.8
75°	66.1
77.5°	31.1
80°	7.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)