

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839707

Luminaire Tested: **LDS4C10D010 EU4109030 4LBCSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C10D010 EU4109030 4LBCSMMS
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBCS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 712.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839707

CATALOG NUMBER: LDS4C10D010 EU4109030 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839707

CATALOG NUMBER: LDS4C10D010 EU4109030 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45935
5°	45777
10°	45271
15°	44490
20°	43497
25°	42333
30°	40997
35°	39414
40°	37431
45°	34036
50°	28096
55°	20691
60°	14030
65°	8227
70°	3233
75°	712
80°	920
85°	1692



TEST NUMBER: P839707

CATALOG NUMBER: LDS4C10D010 EU4109030 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	4.9
10°-20°	98.5	13.8
20°-30°	143.7	20.2
30°-40°	164.0	23.0
40°-50°	149.1	20.9
50°-60°	87.9	12.3
60°-70°	29.5	4.1
70°-80°	3.1	0.4
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.3	39.0
0°-40°	441.3	62.0
0°-60°	678.3	95.3
0°-90°	712.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	712.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	374	
5°	371	35
15°	350	98
25°	312	144
35°	263	164
45°	196	149
55°	97	88
65°	28	29
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P839707

CATALOG NUMBER: LDS4C10D010 EU4109030 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	373.9
2.5°	373.3
5°	371.2
7.5°	367.7
10°	362.9
12.5°	356.7
15°	349.8
17.5°	341.7
20°	332.7
22.5°	322.9
25°	312.3
27.5°	300.7
30°	289.0
32.5°	276.1
35°	262.8
37.5°	248.4
40°	233.4
42.5°	215.9
45°	195.9
47.5°	172.8
50°	147.0
52.5°	121.2
55°	96.6
57.5°	75.6
60°	57.1
62.5°	41.4
65°	28.3
67.5°	17.3
70°	9.0
72.5°	3.5
75°	1.5
77.5°	1.5
80°	1.3
82.5°	1.2
85°	1.2
87.5°	1.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)