

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840014

Luminaire Tested: **LDS4C40D010 EU4409030 4LBSWH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P840014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C40D010 EU4409030 4LBSWH
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH WH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3677.0 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840014

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBSWH

Luminous Intensity Polar Plot





TEST NUMBER: P840014

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBSWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	236247
5°	235164
10°	230311
15°	221929
20°	211717
25°	200308
30°	188942
35°	177902
40°	167510
45°	156158
50°	142389
55°	125750
60°	106440
65°	83575
70°	59627
75°	32657
80°	5731
85°	0



TEST NUMBER: P840014

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBSWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.1	4.9
10°-20°	489.6	13.3
20°-30°	679.9	18.5
30°-40°	741.9	20.2
40°-50°	692.1	18.8
50°-60°	525.4	14.3
60°-70°	287.7	7.8
70°-80°	79.2	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1349.6	36.7
0°-40°	2091.6	56.9
0°-60°	3309.1	90.0
0°-90°	3677.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3677.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1923	
5°	1907	180
15°	1745	490
25°	1478	680
35°	1186	742
45°	899	692
55°	587	525
65°	288	288
75°	69	79
85°	0	1
90°	0	



TEST NUMBER: P840014

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBSWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1923.0
2.5°	1923.0
5°	1906.9
7.5°	1882.6
10°	1846.2
12.5°	1797.6
15°	1744.9
17.5°	1680.2
20°	1619.4
22.5°	1546.5
25°	1477.7
27.5°	1408.9
30°	1331.9
32.5°	1259.1
35°	1186.2
37.5°	1113.3
40°	1044.5
42.5°	971.6
45°	898.8
47.5°	825.9
50°	745.0
52.5°	668.0
55°	587.1
57.5°	510.1
60°	433.2
62.5°	356.3
65°	287.5
67.5°	222.6
70°	166.0
72.5°	113.4
75°	68.8
77.5°	32.4
80°	8.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)