

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840054

Luminaire Tested: **LDS4C45D010 EU4459027 4LBSWH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P840054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C45D010 EU4459027 4LBSWH
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH WH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4094.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840054

CATALOG NUMBER: LDS4C45D010 EU4459027 4LBSWH

Luminous Intensity Polar Plot





TEST NUMBER: P840054

CATALOG NUMBER: LDS4C45D010 EU4459027 4LBSWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	263042
5°	261827
10°	256421
15°	247099
20°	235734
25°	223027
30°	210377
35°	198074
40°	186499
45°	173863
50°	158539
55°	140015
60°	118504
65°	93052
70°	66416
75°	36407
80°	6438
85°	0



TEST NUMBER: P840054

CATALOG NUMBER: LDS4C45D010 EU4459027 4LBSWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.6	4.9
10°-20°	545.1	13.3
20°-30°	757.0	18.5
30°-40°	826.1	20.2
40°-50°	770.6	18.8
50°-60°	584.9	14.3
60°-70°	320.3	7.8
70°-80°	88.1	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1502.7	36.7
0°-40°	2328.8	56.9
0°-60°	3684.3	90.0
0°-90°	4094.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4094.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2141	
5°	2123	201
15°	1943	545
25°	1645	757
35°	1321	826
45°	1001	771
55°	654	585
65°	320	320
75°	77	88
85°	0	1
90°	0	



TEST NUMBER: P840054

CATALOG NUMBER: LDS4C45D010 EU4459027 4LBSWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2141.1
2.5°	2141.1
5°	2123.1
7.5°	2096.1
10°	2055.5
12.5°	2001.5
15°	1942.8
17.5°	1870.8
20°	1803.1
22.5°	1721.9
25°	1645.3
27.5°	1568.7
30°	1483.0
32.5°	1401.9
35°	1320.7
37.5°	1239.6
40°	1162.9
42.5°	1081.8
45°	1000.7
47.5°	919.5
50°	829.5
52.5°	743.7
55°	653.7
57.5°	567.9
60°	482.3
62.5°	396.7
65°	320.1
67.5°	247.9
70°	184.9
72.5°	126.2
75°	76.7
77.5°	36.0
80°	9.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)