

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839752

Luminaire Tested: **LDS4C15D010 EU4159027 4LBSH**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839752  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C15D010 EU4159027 4LBSH  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1459.0 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839752

CATALOG NUMBER: LDS4C15D010 EU4159027 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P839752

CATALOG NUMBER: LDS4C15D010 EU4159027 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93737
5°	93306
10°	91378
15°	88064
20°	84012
25°	79475
30°	74972
35°	70594
40°	66459
45°	61956
50°	56497
55°	49885
60°	42237
65°	33168
70°	23671
75°	12958
80°	2264
85°	0



TEST NUMBER: P839752

CATALOG NUMBER: LDS4C15D010 EU4159027 4LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.5	4.9
10°-20°	194.3	13.3
20°-30°	269.8	18.5
30°-40°	294.4	20.2
40°-50°	274.6	18.8
50°-60°	208.5	14.3
60°-70°	114.1	7.8
70°-80°	31.4	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.5	36.7
0°-40°	829.9	56.9
0°-60°	1313.0	90.0
0°-90°	1459.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1459.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	763	
5°	757	71
15°	692	194
25°	586	270
35°	471	294
45°	357	275
55°	233	208
65°	114	114
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P839752

CATALOG NUMBER: LDS4C15D010 EU4159027 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	763.0
2.5°	763.0
5°	756.6
7.5°	747.0
10°	732.5
12.5°	713.3
15°	692.4
17.5°	666.7
20°	642.6
22.5°	613.7
25°	586.3
27.5°	559.1
30°	528.5
32.5°	499.6
35°	470.7
37.5°	441.8
40°	414.4
42.5°	385.5
45°	356.6
47.5°	327.7
50°	295.6
52.5°	265.1
55°	232.9
57.5°	202.4
60°	171.9
62.5°	141.4
65°	114.1
67.5°	88.3
70°	65.9
72.5°	45.0
75°	27.3
77.5°	12.8
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)