

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840060

Luminaire Tested: **LDS4C45D010 EU4459030 4LBSB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P840060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C45D010 EU4459030 4LBSB
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH B FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2515.0 lumens
Efficiency: N/A
Efficacy: 50.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840060
CATALOG NUMBER: LDS4C45D010 EU4459030 4LBSB

Luminous Intensity Polar Plot





TEST NUMBER: P840060

CATALOG NUMBER: LDS4C45D010 EU4459030 4LBSB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162240
5°	161688
10°	159903
15°	157153
20°	153630
25°	149529
30°	144810
35°	139238
40°	132212
45°	120211
50°	99252
55°	73081
60°	49608
65°	29041
70°	11458
75°	2563
80°	3396
85°	5779



TEST NUMBER: P840060

CATALOG NUMBER: LDS4C45D010 EU4459030 4LBSB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	4.9
10°-20°	347.9	13.8
20°-30°	507.5	20.2
30°-40°	579.3	23.0
40°-50°	526.6	20.9
50°-60°	310.6	12.4
60°-70°	104.2	4.1
70°-80°	10.8	0.4
80°-90°	3.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	979.6	39.0
0°-40°	1558.9	62.0
0°-60°	2396.1	95.3
0°-90°	2515.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2515.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1321	
5°	1311	124
15°	1236	348
25°	1103	507
35°	928	579
45°	692	527
55°	341	311
65°	100	104
75°	5	11
85°	4	4
90°	0	



TEST NUMBER: P840060

CATALOG NUMBER: LDS4C45D010 EU4459030 4LBSB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1320.6
2.5°	1318.5
5°	1311.1
7.5°	1298.8
10°	1281.8
12.5°	1260.1
15°	1235.6
17.5°	1207.1
20°	1175.1
22.5°	1140.5
25°	1103.1
27.5°	1062.3
30°	1020.8
32.5°	975.3
35°	928.4
37.5°	877.4
40°	824.4
42.5°	762.6
45°	691.9
47.5°	610.3
50°	519.3
52.5°	428.2
55°	341.2
57.5°	267.1
60°	201.9
62.5°	146.1
65°	99.9
67.5°	61.2
70°	31.9
72.5°	12.2
75°	5.4
77.5°	5.4
80°	4.8
82.5°	4.1
85°	4.1
87.5°	3.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)