

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839787

Luminaire Tested: **LDS4C15D010 EU4159050 4LBCSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159050 4LBCSMMS
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBCS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1130.9 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839787

CATALOG NUMBER: LDS4C15D010 EU4159050 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839787

CATALOG NUMBER: LDS4C15D010 EU4159050 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72963
5°	72711
10°	71905
15°	70678
20°	69095
25°	67248
30°	65127
35°	62615
40°	59451
45°	54051
50°	44628
55°	32857
60°	22310
65°	13052
70°	5172
75°	1139
80°	1486
85°	2537



TEST NUMBER: P839787

CATALOG NUMBER: LDS4C15D010 EU4159050 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	4.9
10°-20°	156.5	13.8
20°-30°	228.2	20.2
30°-40°	260.5	23.0
40°-50°	236.8	20.9
50°-60°	139.7	12.4
60°-70°	46.8	4.1
70°-80°	4.9	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	440.6	39.0
0°-40°	701.1	62.0
0°-60°	1077.6	95.3
0°-90°	1130.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1130.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	594	
5°	590	56
15°	556	156
25°	496	228
35°	418	261
45°	311	237
55°	153	140
65°	45	47
75°	2	5
85°	2	2
90°	0	



TEST NUMBER: P839787

CATALOG NUMBER: LDS4C15D010 EU4159050 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	593.9
2.5°	593.0
5°	589.6
7.5°	584.1
10°	576.4
12.5°	566.7
15°	555.7
17.5°	542.8
20°	528.5
22.5°	512.9
25°	496.1
27.5°	477.7
30°	459.1
32.5°	438.6
35°	417.5
37.5°	394.6
40°	370.7
42.5°	342.9
45°	311.1
47.5°	274.5
50°	233.5
52.5°	192.6
55°	153.4
57.5°	120.1
60°	90.8
62.5°	65.7
65°	44.9
67.5°	27.5
70°	14.4
72.5°	5.5
75°	2.4
77.5°	2.4
80°	2.1
82.5°	1.8
85°	1.8
87.5°	1.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)