

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840086

Luminaire Tested: **LDS4C45D010 EU4459050 4LBCSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P840086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C45D010 EU4459050 4LBCSMB
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBCS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3337.0 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840086

CATALOG NUMBER: LDS4C45D010 EU4459050 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P840086

CATALOG NUMBER: LDS4C45D010 EU4459050 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215264
5°	214532
10°	212173
15°	208524
20°	203847
25°	198397
30°	192148
35°	184756
40°	175433
45°	159494
50°	131686
55°	96963
60°	65800
65°	38546
70°	15230
75°	3418
80°	4457
85°	7612



TEST NUMBER: P840086

CATALOG NUMBER: LDS4C45D010 EU4459050 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.8	4.9
10°-20°	461.6	13.8
20°-30°	673.4	20.2
30°-40°	768.6	23.0
40°-50°	698.7	20.9
50°-60°	412.1	12.3
60°-70°	138.2	4.1
70°-80°	14.4	0.4
80°-90°	5.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1299.8	39.0
0°-40°	2068.4	62.0
0°-60°	3179.3	95.3
0°-90°	3337.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3337.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1752	
5°	1740	165
15°	1640	462
25°	1464	673
35°	1232	769
45°	918	699
55°	453	412
65°	133	138
75°	7	14
85°	5	5
90°	0	



TEST NUMBER: P840086

CATALOG NUMBER: LDS4C45D010 EU4459050 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1752.2
2.5°	1749.5
5°	1739.6
7.5°	1723.3
10°	1700.8
12.5°	1671.9
15°	1639.5
17.5°	1601.6
20°	1559.2
22.5°	1513.2
25°	1463.6
27.5°	1409.5
30°	1354.5
32.5°	1294.1
35°	1231.9
37.5°	1164.2
40°	1093.9
42.5°	1011.8
45°	918.0
47.5°	809.8
50°	689.0
52.5°	568.1
55°	452.7
57.5°	354.4
60°	267.8
62.5°	193.9
65°	132.6
67.5°	81.2
70°	42.4
72.5°	16.2
75°	7.2
77.5°	7.2
80°	6.3
82.5°	5.4
85°	5.4
87.5°	4.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)