

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856693

Luminaire Tested: **LD4C10D010 EU4109027 4LBMLI**

Issue Date: 7/19/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P856693  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/19/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10D010 EU4109027 4LBMLI  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 910.0 lumens  
Efficiency: N/A  
Efficacy: 92.9 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856693

CATALOG NUMBER: LD4C10D010 EU4109027 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856693

CATALOG NUMBER: LD4C10D010 EU4109027 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88		
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83		
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78		
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73		
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69		
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65		
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62		
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58		
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	176246
5°	173244
10°	159179
15°	133305
20°	106800
25°	85819
30°	63879
35°	36489
40°	17128
45°	7280
50°	2313
55°	1178
60°	811
65°	640
70°	395
75°	0
80°	0
85°	0



TEST NUMBER: P856693

CATALOG NUMBER: LD4C10D010 EU4109027 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.9	14.3
10°-20°	290.4	31.9
20°-30°	288.7	31.7
30°-40°	157.2	17.3
40°-50°	36.3	4.0
50°-60°	5.1	0.6
60°-70°	1.9	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.0	77.9
0°-40°	866.2	95.2
0°-60°	907.6	99.7
0°-90°	910.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1435	
5°	1405	130
15°	1048	290
25°	633	289
35°	243	157
45°	42	36
55°	6	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856693

CATALOG NUMBER: LD4C10D010 EU4109027 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1434.6
2.5°	1431.3
5°	1404.8
7.5°	1350.9
10°	1276.0
12.5°	1165.9
15°	1048.1
17.5°	931.4
20°	816.9
22.5°	723.3
25°	633.1
27.5°	547.2
30°	450.3
32.5°	342.4
35°	243.3
37.5°	164.0
40°	106.8
42.5°	67.1
45°	41.9
47.5°	24.2
50°	12.1
52.5°	6.6
55°	5.5
57.5°	3.3
60°	3.3
62.5°	2.2
65°	2.2
67.5°	1.1
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)