

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839838

Luminaire Tested: **LDS4C20D010 EU4209050 4LBPSMB**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839838  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C20D010 EU4209050 4LBPSMB  
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBPS TRIM WITH MB FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1621.0 lumens  
Efficiency: N/A  
Efficacy: 74.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839838

CATALOG NUMBER: LDS4C20D010 EU4209050 4LBPSMB

### Luminous Intensity Polar Plot





TEST NUMBER: P839838

CATALOG NUMBER: LDS4C20D010 EU4209050 4LBPSMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49		
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44		
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	104573
5°	104208
10°	103067
15°	101292
20°	99021
25°	96379
30°	93343
35°	89746
40°	85223
45°	77471
50°	63970
55°	47100
60°	31966
65°	18721
70°	7400
75°	1661
80°	2193
85°	3665



TEST NUMBER: P839838

CATALOG NUMBER: LDS4C20D010 EU4209050 4LBPSMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.1	4.9
10°-20°	224.3	13.8
20°-30°	327.1	20.2
30°-40°	373.4	23.0
40°-50°	339.4	20.9
50°-60°	200.2	12.4
60°-70°	67.1	4.1
70°-80°	7.0	0.4
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	631.4	39.0
0°-40°	1004.8	62.0
0°-60°	1544.4	95.3
0°-90°	1621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1621.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	851	
5°	845	80
15°	796	224
25°	711	327
35°	598	373
45°	446	339
55°	220	200
65°	64	67
75°	4	7
85°	3	2
90°	0	



TEST NUMBER: P839838

CATALOG NUMBER: LDS4C20D010 EU4209050 4LBPSMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	851.2
2.5°	849.8
5°	845.0
7.5°	837.1
10°	826.2
12.5°	812.2
15°	796.4
17.5°	778.0
20°	757.4
22.5°	735.1
25°	711.0
27.5°	684.7
30°	658.0
32.5°	628.6
35°	598.4
37.5°	565.5
40°	531.4
42.5°	491.5
45°	445.9
47.5°	393.4
50°	334.7
52.5°	276.0
55°	219.9
57.5°	172.2
60°	130.1
62.5°	94.2
65°	64.4
67.5°	39.4
70°	20.6
72.5°	7.9
75°	3.5
77.5°	3.5
80°	3.1
82.5°	2.6
85°	2.6
87.5°	2.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)