

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856724

Luminaire Tested: **LX4C10D010 EX4C109030 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P856724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109030 4LBMLI
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 946.0 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856724

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P856724

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299087
5°	269140
10°	208642
15°	151022
20°	104564
25°	76235
30°	55396
35°	32770
40°	13792
45°	4291
50°	554
55°	321
60°	369
65°	436
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856724

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.9	20.3
10°-20°	328.4	34.7
20°-30°	261.0	27.6
30°-40°	138.2	14.6
40°-50°	23.8	2.5
50°-60°	1.8	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	781.3	82.6
0°-40°	919.5	97.2
0°-60°	945.1	99.9
0°-90°	946.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	946.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2434	
5°	2182	192
15°	1187	328
25°	562	261
35°	218	138
45°	25	24
55°	2	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856724

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2434.5
2.5°	2371.8
5°	2182.4
7.5°	1934.8
10°	1672.5
12.5°	1419.0
15°	1187.4
17.5°	971.7
20°	799.8
22.5°	668.7
25°	562.4
27.5°	476.4
30°	390.5
32.5°	303.0
35°	218.5
37.5°	144.3
40°	86.0
42.5°	49.5
45°	24.7
47.5°	8.8
50°	2.9
52.5°	2.9
55°	1.5
57.5°	1.5
60°	1.5
62.5°	1.5
65°	1.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)