

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839863

Luminaire Tested: **LDS4C25D010 EU4259030 4LBSLI**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C25D010 EU4259030 4LBSLI
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2563.0 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839863

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839863

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	224834
5°	219736
10°	206347
15°	191976
20°	178052
25°	162312
30°	144498
35°	128080
40°	115116
45°	103028
50°	88396
55°	71111
60°	52974
65°	33837
70°	16308
75°	2706
80°	1981
85°	0



TEST NUMBER: P839863

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.9	6.5
10°-20°	423.2	16.5
20°-30°	548.4	21.4
30°-40°	537.3	21.0
40°-50°	455.4	17.8
50°-60°	298.6	11.6
60°-70°	120.0	4.7
70°-80°	13.7	0.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1137.5	44.4
0°-40°	1674.9	65.3
0°-60°	2428.9	94.8
0°-90°	2563.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2563.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1830	
5°	1782	166
15°	1509	423
25°	1197	548
35°	854	537
45°	593	455
55°	332	299
65°	116	120
75°	6	14
85°	0	0
90°	0	



TEST NUMBER: P839863

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1830.1
2.5°	1815.9
5°	1781.8
7.5°	1725.0
10°	1654.1
12.5°	1577.5
15°	1509.4
17.5°	1435.7
20°	1361.9
22.5°	1282.5
25°	1197.4
27.5°	1109.4
30°	1018.6
32.5°	933.5
35°	854.0
37.5°	788.8
40°	717.8
42.5°	655.4
45°	593.0
47.5°	527.7
50°	462.5
52.5°	397.2
55°	332.0
57.5°	272.4
60°	215.6
62.5°	164.5
65°	116.4
67.5°	76.6
70°	45.4
72.5°	19.8
75°	5.7
77.5°	2.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)