

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839867

Luminaire Tested: **LDS4C25D010 EU4259035 4LBCSMMS**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C25D010 EU4259035 4LBCSMMS
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBCS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1793.0 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839867

CATALOG NUMBER: LDS4C25D010 EU4259035 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839867

CATALOG NUMBER: LDS4C25D010 EU4259035 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70																			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62																			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55																			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115667
5°	115270
10°	114008
15°	112039
20°	109532
25°	106600
30°	103245
35°	99269
40°	94268
45°	85706
50°	70755
55°	52091
60°	35357
65°	20698
70°	8190
75°	1851
80°	2405
85°	4088



TEST NUMBER: P839867

CATALOG NUMBER: LDS4C25D010 EU4259035 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	4.9
10°-20°	248.0	13.8
20°-30°	361.8	20.2
30°-40°	413.0	23.0
40°-50°	375.5	20.9
50°-60°	221.4	12.3
60°-70°	74.3	4.1
70°-80°	7.8	0.4
80°-90°	2.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	698.4	39.0
0°-40°	1111.4	62.0
0°-60°	1708.3	95.3
0°-90°	1793.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1793.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	942	
5°	935	89
15°	881	248
25°	786	362
35°	662	413
45°	493	375
55°	243	221
65°	71	74
75°	4	8
85°	3	3
90°	0	



TEST NUMBER: P839867

CATALOG NUMBER: LDS4C25D010 EU4259035 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	941.5
2.5°	940.0
5°	934.7
7.5°	926.0
10°	913.9
12.5°	898.3
15°	880.9
17.5°	860.6
20°	837.8
22.5°	813.1
25°	786.4
27.5°	757.3
30°	727.8
32.5°	695.3
35°	661.9
37.5°	625.5
40°	587.8
42.5°	543.7
45°	493.3
47.5°	435.1
50°	370.2
52.5°	305.3
55°	243.2
57.5°	190.4
60°	143.9
62.5°	104.2
65°	71.2
67.5°	43.6
70°	22.8
72.5°	8.7
75°	3.9
77.5°	3.9
80°	3.4
82.5°	2.9
85°	2.9
87.5°	2.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)