

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856794

Luminaire Tested: **LX4C10D010 EX4C109050 4LBNH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P856794  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C10D010 EX4C109050 4LBNH  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 653.0 lumens  
Efficiency: N/A  
Efficacy: 66.6 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856794

CATALOG NUMBER: LX4C10D010 EX4C109050 4LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P856794

CATALOG NUMBER: LX4C10D010 EX4C109050 4LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100728
5°	98486
10°	91054
15°	81705
20°	71919
25°	61894
30°	49849
35°	33190
40°	17256
45°	7818
50°	3383
55°	2270
60°	1450
65°	1047
70°	862
75°	570
80°	0
85°	0



TEST NUMBER: P856794

CATALOG NUMBER: LX4C10D010 EX4C109050 4LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.0	11.3
10°-20°	179.4	27.5
20°-30°	208.3	31.9
30°-40°	138.0	21.1
40°-50°	38.7	5.9
50°-60°	9.7	1.5
60°-70°	3.7	0.6
70°-80°	1.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.7	70.7
0°-40°	599.7	91.8
0°-60°	648.1	99.2
0°-90°	653.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	653.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	820	
5°	799	74
15°	642	179
25°	457	208
35°	221	138
45°	45	39
55°	11	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P856794

CATALOG NUMBER: LX4C10D010 EX4C109050 4LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	819.9
2.5°	816.3
5°	798.6
7.5°	767.8
10°	729.9
12.5°	687.3
15°	642.4
17.5°	598.6
20°	550.1
22.5°	505.2
25°	456.6
27.5°	410.5
30°	351.4
32.5°	288.7
35°	221.3
37.5°	158.5
40°	107.6
42.5°	69.8
45°	45.0
47.5°	27.2
50°	17.7
52.5°	13.0
55°	10.6
57.5°	8.3
60°	5.9
62.5°	4.7
65°	3.6
67.5°	2.4
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)