

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839876

Luminaire Tested: **LDS4C25D010 EU4259040 4LBCSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C25D010 EU4259040 4LBCSMB
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBCS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1756.0 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839876

CATALOG NUMBER: LDS4C25D010 EU4259040 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839876

CATALOG NUMBER: LDS4C25D010 EU4259040 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113271
5°	112890
10°	111650
15°	109724
20°	107270
25°	104404
30°	101117
35°	97215
40°	92311
45°	83934
50°	69302
55°	51020
60°	34620
65°	20291
70°	8010
75°	1804
80°	2335
85°	3947



TEST NUMBER: P839876

CATALOG NUMBER: LDS4C25D010 EU4259040 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	4.9
10°-20°	242.9	13.8
20°-30°	354.3	20.2
30°-40°	404.5	23.0
40°-50°	367.7	20.9
50°-60°	216.9	12.4
60°-70°	72.7	4.1
70°-80°	7.6	0.4
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	684.0	39.0
0°-40°	1088.5	62.0
0°-60°	1673.0	95.3
0°-90°	1756.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1756.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	922	
5°	915	87
15°	863	243
25°	770	354
35°	648	404
45°	483	368
55°	238	217
65°	70	73
75°	4	8
85°	3	3
90°	0	



TEST NUMBER: P839876

CATALOG NUMBER: LDS4C25D010 EU4259040 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	922.0
2.5°	920.6
5°	915.4
7.5°	906.9
10°	895.0
12.5°	879.8
15°	862.7
17.5°	842.8
20°	820.5
22.5°	796.3
25°	770.2
27.5°	741.7
30°	712.8
32.5°	681.0
35°	648.2
37.5°	612.6
40°	575.6
42.5°	532.4
45°	483.1
47.5°	426.1
50°	362.6
52.5°	299.0
55°	238.2
57.5°	186.5
60°	140.9
62.5°	102.0
65°	69.8
67.5°	42.7
70°	22.3
72.5°	8.5
75°	3.8
77.5°	3.8
80°	3.3
82.5°	2.8
85°	2.8
87.5°	2.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)