

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856800

Luminaire Tested: **LX4C10D010 EX4C109050 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P856800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109050 4LBWLI
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1034.0 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856800

CATALOG NUMBER: LX4C10D010 EX4C109050 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856800

CATALOG NUMBER: LX4C10D010 EX4C109050 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P856800

CATALOG NUMBER: LX4C10D010 EX4C109050 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	6.0
10°-20°	195.5	18.9
20°-30°	305.0	29.5
30°-40°	296.8	28.7
40°-50°	148.2	14.3
50°-60°	23.0	2.2
60°-70°	2.8	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.5	54.4
0°-40°	859.3	83.1
0°-60°	1030.4	99.7
0°-90°	1034.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1034.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	634	
5°	642	62
15°	690	196
25°	670	305
35°	482	297
45°	186	148
55°	19	23
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P856800

CATALOG NUMBER: LX4C10D010 EX4C109050 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	633.5
2.5°	635.9
5°	641.8
7.5°	651.3
10°	663.2
12.5°	678.5
15°	690.4
17.5°	699.9
20°	701.1
22.5°	692.8
25°	670.3
27.5°	637.1
30°	595.6
32.5°	543.6
35°	482.0
37.5°	414.4
40°	343.4
42.5°	267.6
45°	185.9
47.5°	119.6
50°	72.2
52.5°	39.1
55°	19.0
57.5°	8.3
60°	4.7
62.5°	3.6
65°	2.4
67.5°	2.4
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)