

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839897

Luminaire Tested: **LDS4C30D010 EU4309027 4LBCSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309027 4LBCSMMS
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBCS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1997.0 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839897

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839897

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128824
5°	128379
10°	126969
15°	124783
20°	121992
25°	118732
30°	114991
35°	110563
40°	104981
45°	95453
50°	78801
55°	58024
60°	39387
65°	23052
70°	9124
75°	2041
80°	2688
85°	4511



TEST NUMBER: P839897

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.6	4.9
10°-20°	276.3	13.8
20°-30°	403.0	20.2
30°-40°	460.0	23.0
40°-50°	418.2	20.9
50°-60°	246.6	12.4
60°-70°	82.7	4.1
70°-80°	8.6	0.4
80°-90°	3.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.9	39.0
0°-40°	1237.8	62.0
0°-60°	1902.6	95.3
0°-90°	1997.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1997.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1049	
5°	1041	99
15°	981	276
25°	876	403
35°	737	460
45°	549	418
55°	271	247
65°	79	83
75°	4	9
85°	3	3
90°	0	



TEST NUMBER: P839897

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1048.6
2.5°	1047.0
5°	1041.0
7.5°	1031.3
10°	1017.8
12.5°	1000.6
15°	981.1
17.5°	958.5
20°	933.1
22.5°	905.6
25°	875.9
27.5°	843.5
30°	810.6
32.5°	774.4
35°	737.2
37.5°	696.7
40°	654.6
42.5°	605.5
45°	549.4
47.5°	484.6
50°	412.3
52.5°	340.0
55°	270.9
57.5°	212.1
60°	160.3
62.5°	116.0
65°	79.3
67.5°	48.6
70°	25.4
72.5°	9.7
75°	4.3
77.5°	4.3
80°	3.8
82.5°	3.2
85°	3.2
87.5°	2.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)