

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856824

Luminaire Tested: **LX4C10D010 EX4C109830 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P856824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109830 4LBMH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 675.9 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856824

CATALOG NUMBER: LX4C10D010 EX4C109830 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P856824

CATALOG NUMBER: LX4C10D010 EX4C109830 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53527
5°	53732
10°	53891
15°	53902
20°	53589
25°	52337
30°	48913
35°	42368
40°	33085
45°	23750
50°	15424
55°	9232
60°	5406
65°	3459
70°	2299
75°	1756
80°	1344
85°	0



TEST NUMBER: P856824

CATALOG NUMBER: LX4C10D010 EX4C109830 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	6.1
10°-20°	119.5	17.7
20°-30°	176.4	26.1
30°-40°	174.1	25.8
40°-50°	106.5	15.8
50°-60°	40.8	6.0
60°-70°	12.8	1.9
70°-80°	3.8	0.6
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.4	49.9
0°-40°	511.5	75.7
0°-60°	658.9	97.5
0°-90°	675.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	675.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	436	
5°	436	41
15°	424	120
25°	386	176
35°	282	174
45°	137	107
55°	43	41
65°	12	13
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P856824

CATALOG NUMBER: LX4C10D010 EX4C109830 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	435.7
2.5°	436.6
5°	435.7
7.5°	434.7
10°	432.0
12.5°	428.3
15°	423.8
17.5°	418.2
20°	409.9
22.5°	400.8
25°	386.1
27.5°	367.8
30°	344.8
32.5°	316.5
35°	282.5
37.5°	244.9
40°	206.3
42.5°	170.6
45°	136.7
47.5°	106.4
50°	80.7
52.5°	59.7
55°	43.1
57.5°	30.2
60°	22.0
62.5°	16.5
65°	11.9
67.5°	9.2
70°	6.4
72.5°	4.5
75°	3.7
77.5°	1.9
80°	1.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)