

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839901

Luminaire Tested: **LDS4C30D010 EU4309027 4LBSGPH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309027 4LBSGPH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH GPH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1839.0 lumens
Efficiency: N/A
Efficacy: 58.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839901

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBSGPH

Luminous Intensity Polar Plot





TEST NUMBER: P839901

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBSGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																											
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																											
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70																											
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62																											
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55																											
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49																											
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																											
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																											
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36																											
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118627
5°	118230
10°	116927
15°	114914
20°	112343
25°	109338
30°	105898
35°	101819
40°	96673
45°	87896
50°	72571
55°	53440
60°	36266
65°	21250
70°	8405
75°	1899
80°	2476
85°	4229



TEST NUMBER: P839901

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBSGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	4.9
10°-20°	254.4	13.8
20°-30°	371.1	20.2
30°-40°	423.6	23.0
40°-50°	385.1	20.9
50°-60°	227.1	12.3
60°-70°	76.2	4.1
70°-80°	8.0	0.4
80°-90°	2.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	716.3	39.0
0°-40°	1139.9	62.0
0°-60°	1752.1	95.3
0°-90°	1839.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1839.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	966	
5°	959	91
15°	904	254
25°	807	371
35°	679	424
45°	506	385
55°	250	227
65°	73	76
75°	4	8
85°	3	3
90°	0	



TEST NUMBER: P839901

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBSGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	965.6
2.5°	964.1
5°	958.7
7.5°	949.7
10°	937.3
12.5°	921.4
15°	903.5
17.5°	882.6
20°	859.3
22.5°	833.9
25°	806.6
27.5°	776.8
30°	746.5
32.5°	713.2
35°	678.9
37.5°	641.6
40°	602.8
42.5°	557.6
45°	505.9
47.5°	446.3
50°	379.7
52.5°	313.1
55°	249.5
57.5°	195.3
60°	147.6
62.5°	106.8
65°	73.1
67.5°	44.7
70°	23.4
72.5°	8.9
75°	4.0
77.5°	4.0
80°	3.5
82.5°	3.0
85°	3.0
87.5°	2.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)