

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856835

Luminaire Tested: **LX4C10D010 EX4C109835 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P856835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109835 4LBMDH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 648.3 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856835

CATALOG NUMBER: LX4C10D010 EX4C109835 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P856835

CATALOG NUMBER: LX4C10D010 EX4C109835 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	80	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	63	60	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	74	65	60	56	64	59	56	64	59	56	63	58	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95949
5°	94650
10°	90218
15°	83473
20°	75148
25°	62436
30°	45381
35°	29425
40°	17801
45°	9174
50°	4167
55°	2506
60°	1695
65°	1192
70°	898
75°	570
80°	354
85°	282



TEST NUMBER: P856835

CATALOG NUMBER: LX4C10D010 EX4C109835 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.9	11.1
10°-20°	183.1	28.3
20°-30°	207.1	31.9
30°-40°	125.2	19.3
40°-50°	43.8	6.8
50°-60°	11.2	1.7
60°-70°	4.3	0.7
70°-80°	1.4	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.1	71.3
0°-40°	587.3	90.6
0°-60°	642.4	99.1
0°-90°	648.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	648.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	781	
5°	768	72
15°	656	183
25°	461	207
35°	196	125
45°	53	44
55°	12	11
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P856835

CATALOG NUMBER: LX4C10D010 EX4C109835 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	781.0
2.5°	777.8
5°	767.5
7.5°	749.4
10°	723.2
12.5°	691.5
15°	656.3
17.5°	617.7
20°	574.8
22.5°	522.2
25°	460.6
27.5°	390.0
30°	319.9
32.5°	252.9
35°	196.2
37.5°	148.7
40°	111.0
42.5°	79.7
45°	52.8
47.5°	32.5
50°	21.8
52.5°	15.6
55°	11.7
57.5°	9.0
60°	6.9
62.5°	5.4
65°	4.1
67.5°	3.2
70°	2.5
72.5°	1.8
75°	1.2
77.5°	0.9
80°	0.5
82.5°	0.4
85°	0.2
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)