

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839907

Luminaire Tested: **LDS4C30D010 EU4309030 4LBCSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309030 4LBCSMMS
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBCS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2076.0 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839907

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839907

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133923
5°	133460
10°	131997
15°	129718
20°	126816
25°	123422
30°	119545
35°	114942
40°	109134
45°	99224
50°	81917
55°	60315
60°	40935
65°	23982
70°	9483
75°	2136
80°	2759
85°	4793



TEST NUMBER: P839907

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.5	4.9
10°-20°	287.2	13.8
20°-30°	418.9	20.2
30°-40°	478.2	23.0
40°-50°	434.7	20.9
50°-60°	256.4	12.3
60°-70°	86.0	4.1
70°-80°	9.0	0.4
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.6	39.0
0°-40°	1286.8	62.0
0°-60°	1977.9	95.3
0°-90°	2076.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2076.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1090	
5°	1082	103
15°	1020	287
25°	910	419
35°	766	478
45°	571	435
55°	282	256
65°	82	86
75°	4	9
85°	3	3
90°	0	



TEST NUMBER: P839907

CATALOG NUMBER: LDS4C30D010 EU4309030 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1090.1
2.5°	1088.4
5°	1082.2
7.5°	1072.1
10°	1058.1
12.5°	1040.1
15°	1019.9
17.5°	996.4
20°	970.0
22.5°	941.4
25°	910.5
27.5°	876.9
30°	842.7
32.5°	805.1
35°	766.4
37.5°	724.3
40°	680.5
42.5°	629.5
45°	571.1
47.5°	503.8
50°	428.6
52.5°	353.4
55°	281.6
57.5°	220.5
60°	166.6
62.5°	120.6
65°	82.5
67.5°	50.5
70°	26.4
72.5°	10.1
75°	4.5
77.5°	4.5
80°	3.9
82.5°	3.4
85°	3.4
87.5°	2.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)