

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839944

Luminaire Tested: **LDS4C30D010 EU4309050 4LBSWH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839944
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309050 4LBSWH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH WH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2782.0 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839944

CATALOG NUMBER: LDS4C30D010 EU4309050 4LBSWH

Luminous Intensity Polar Plot





TEST NUMBER: P839944

CATALOG NUMBER: LDS4C30D010 EU4309050 4LBSWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178752
5°	177918
10°	174249
15°	167913
20°	160180
25°	151549
30°	142951
35°	134604
40°	126743
45°	118144
50°	107719
55°	95143
60°	80543
65°	63226
70°	45115
75°	24730
80°	4386
85°	0



TEST NUMBER: P839944

CATALOG NUMBER: LDS4C30D010 EU4309050 4LBSWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.3	4.9
10°-20°	370.4	13.3
20°-30°	514.4	18.5
30°-40°	561.4	20.2
40°-50°	523.7	18.8
50°-60°	397.5	14.3
60°-70°	217.6	7.8
70°-80°	59.9	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1021.1	36.7
0°-40°	1582.5	56.9
0°-60°	2503.6	90.0
0°-90°	2782.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2782.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1455	
5°	1443	136
15°	1320	370
25°	1118	514
35°	898	561
45°	680	524
55°	444	397
65°	218	218
75°	52	60
85°	0	1
90°	0	



TEST NUMBER: P839944

CATALOG NUMBER: LDS4C30D010 EU4309050 4LBSWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1455.0
2.5°	1455.0
5°	1442.7
7.5°	1424.4
10°	1396.8
12.5°	1360.1
15°	1320.2
17.5°	1271.2
20°	1225.2
22.5°	1170.1
25°	1118.0
27.5°	1066.0
30°	1007.7
32.5°	952.6
35°	897.5
37.5°	842.3
40°	790.3
42.5°	735.1
45°	680.0
47.5°	624.9
50°	563.6
52.5°	505.4
55°	444.2
57.5°	385.9
60°	327.8
62.5°	269.6
65°	217.5
67.5°	168.4
70°	125.6
72.5°	85.8
75°	52.1
77.5°	24.5
80°	6.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)