

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856862

Luminaire Tested: **LX4C10D010 EX4C109850 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P856862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109850 4LBMDLI
Description:
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 769.6 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856862
CATALOG NUMBER: LX4C10D010 EX4C109850 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P856862

CATALOG NUMBER: LX4C10D010 EX4C109850 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124180
5°	128404
10°	129714
15°	116847
20°	97099
25°	76181
30°	55751
35°	28810
40°	13680
45°	4813
50°	1089
55°	707
60°	516
65°	349
70°	251
75°	190
80°	141
85°	0



TEST NUMBER: P856862

CATALOG NUMBER: LX4C10D010 EX4C109850 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	12.9
10°-20°	253.0	32.9
20°-30°	256.1	33.3
30°-40°	130.5	17.0
40°-50°	25.6	3.3
50°-60°	3.1	0.4
60°-70°	1.3	0.2
70°-80°	0.5	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.5	79.1
0°-40°	739.1	96.0
0°-60°	767.8	99.8
0°-90°	769.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	769.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1011	
5°	1041	99
15°	919	253
25°	562	256
35°	192	131
45°	28	26
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856862

CATALOG NUMBER: LX4C10D010 EX4C109850 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1010.8
2.5°	1020.2
5°	1041.2
7.5°	1053.3
10°	1039.8
12.5°	994.1
15°	918.7
17.5°	829.7
20°	742.7
22.5°	652.7
25°	562.0
27.5°	471.7
30°	393.0
32.5°	296.1
35°	192.1
37.5°	128.6
40°	85.3
42.5°	53.6
45°	27.7
47.5°	9.9
50°	5.7
52.5°	4.2
55°	3.3
57.5°	2.6
60°	2.1
62.5°	1.7
65°	1.2
67.5°	0.9
70°	0.7
72.5°	0.5
75°	0.4
77.5°	0.4
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)