

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839951

Luminaire Tested: **LDS4C35D010 EU4359027 4LBSGPH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359027 4LBSGPH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH GPH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2170.0 lumens
Efficiency: N/A
Efficacy: 53.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839951

CATALOG NUMBER: LDS4C35D010 EU4359027 4LBSGPH

Luminous Intensity Polar Plot





TEST NUMBER: P839951

CATALOG NUMBER: LDS4C35D010 EU4359027 4LBSGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139979
5°	139503
10°	137972
15°	135594
20°	132555
25°	129020
30°	124949
35°	120146
40°	114074
45°	103723
50°	85624
55°	63057
60°	42802
65°	25058
70°	9914
75°	2231
80°	2901
85°	4934



TEST NUMBER: P839951

CATALOG NUMBER: LDS4C35D010 EU4359027 4LBSGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	4.9
10°-20°	300.2	13.8
20°-30°	437.9	20.2
30°-40°	499.8	23.0
40°-50°	454.4	20.9
50°-60°	268.0	12.3
60°-70°	89.9	4.1
70°-80°	9.4	0.4
80°-90°	3.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	845.3	39.0
0°-40°	1345.1	62.0
0°-60°	2067.5	95.3
0°-90°	2170.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2170.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1139	
5°	1131	107
15°	1066	300
25°	952	438
35°	801	500
45°	597	454
55°	294	268
65°	86	90
75°	5	9
85°	4	3
90°	0	



TEST NUMBER: P839951

CATALOG NUMBER: LDS4C35D010 EU4359027 4LBSGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1139.4
2.5°	1137.7
5°	1131.2
7.5°	1120.7
10°	1106.0
12.5°	1087.2
15°	1066.1
17.5°	1041.5
20°	1013.9
22.5°	984.0
25°	951.8
27.5°	916.6
30°	880.8
32.5°	841.5
35°	801.1
37.5°	757.1
40°	711.3
42.5°	658.0
45°	597.0
47.5°	526.6
50°	448.0
52.5°	369.4
55°	294.4
57.5°	230.5
60°	174.2
62.5°	126.1
65°	86.2
67.5°	52.8
70°	27.6
72.5°	10.6
75°	4.7
77.5°	4.7
80°	4.1
82.5°	3.5
85°	3.5
87.5°	2.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)