

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839959

Luminaire Tested: **LDS4C35D010 EU4359030 4LBPSMMS**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359030 4LBPSMMS
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2783.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839959

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839959

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																											
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																											
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70																											
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62																											
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55																											
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49																											
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																											
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																											
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36																											
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179526
5°	178917
10°	176944
15°	173903
20°	170012
25°	165457
30°	160244
35°	154071
40°	146309
45°	133016
50°	109821
55°	80856
60°	54891
65°	32151
70°	12680
75°	2848
80°	3750
85°	6343



TEST NUMBER: P839959

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.5	4.9
10°-20°	385.0	13.8
20°-30°	561.6	20.2
30°-40°	641.0	23.0
40°-50°	582.7	20.9
50°-60°	343.7	12.4
60°-70°	115.3	4.1
70°-80°	12.0	0.4
80°-90°	4.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1084.0	39.0
0°-40°	1725.0	62.0
0°-60°	2651.5	95.3
0°-90°	2783.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2783.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1461	
5°	1451	137
15°	1367	385
25°	1221	562
35°	1027	641
45°	766	583
55°	378	344
65°	111	115
75°	6	12
85°	4	4
90°	0	



TEST NUMBER: P839959

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1461.3
2.5°	1459.0
5°	1450.8
7.5°	1437.2
10°	1418.4
12.5°	1394.4
15°	1367.3
17.5°	1335.7
20°	1300.4
22.5°	1262.0
25°	1220.6
27.5°	1175.5
30°	1129.6
32.5°	1079.2
35°	1027.3
37.5°	970.9
40°	912.3
42.5°	843.8
45°	765.6
47.5°	675.4
50°	574.6
52.5°	473.8
55°	377.5
57.5°	295.6
60°	223.4
62.5°	161.7
65°	110.6
67.5°	67.7
70°	35.3
72.5°	13.5
75°	6.0
77.5°	6.0
80°	5.3
82.5°	4.5
85°	4.5
87.5°	3.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)