

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839961

Luminaire Tested: **LDS4C35D010 EU4359030 4LBSGPH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359030 4LBSGPH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH GPH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2256.1 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839961

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBSGPH

Luminous Intensity Polar Plot





TEST NUMBER: P839961

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBSGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145532
5°	145028
10°	143436
15°	140974
20°	137811
25°	134130
30°	129900
35°	124900
40°	118596
45°	107824
50°	89027
55°	65563
60°	44498
65°	26046
70°	10309
75°	2326
80°	3042
85°	5215



TEST NUMBER: P839961

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBSGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.4	4.9
10°-20°	312.1	13.8
20°-30°	455.2	20.2
30°-40°	519.6	23.0
40°-50°	472.4	20.9
50°-60°	278.6	12.4
60°-70°	93.5	4.1
70°-80°	9.8	0.4
80°-90°	3.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	878.8	39.0
0°-40°	1398.4	62.0
0°-60°	2149.4	95.3
0°-90°	2256.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2256.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1185	
5°	1176	111
15°	1108	312
25°	990	455
35°	833	520
45°	621	472
55°	306	279
65°	90	93
75°	5	10
85°	4	3
90°	0	



TEST NUMBER: P839961

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBSGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1184.6
2.5°	1182.8
5°	1176.0
7.5°	1165.1
10°	1149.8
12.5°	1130.3
15°	1108.4
17.5°	1082.8
20°	1054.1
22.5°	1023.0
25°	989.5
27.5°	952.9
30°	915.7
32.5°	874.9
35°	832.8
37.5°	787.1
40°	739.5
42.5°	684.0
45°	620.6
47.5°	547.5
50°	465.8
52.5°	384.1
55°	306.1
57.5°	239.6
60°	181.1
62.5°	131.1
65°	89.6
67.5°	54.9
70°	28.7
72.5°	11.0
75°	4.9
77.5°	4.9
80°	4.3
82.5°	3.7
85°	3.7
87.5°	3.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)