

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857162

Luminaire Tested: **LX4C20D010 EU4209035 4LBHYLI**

Issue Date: 7/20/2023



Test Information

Test Method: LM-79-08
Report Number: P857162
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EU4209035 4LBHYLI
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1595.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857162

CATALOG NUMBER: LX4C20D010 EU4209035 4LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P857162

CATALOG NUMBER: LX4C20D010 EU4209035 4LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	76			
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	72	71			
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	606171
5°	590864
10°	500941
15°	324696
20°	201637
25°	108524
30°	37295
35°	15028
40°	4009
45°	1790
50°	707
55°	321
60°	172
65°	203
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857162

CATALOG NUMBER: LX4C20D010 EU4209035 4LBHYLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	432.1	27.1
10°-20°	712.8	44.7
20°-30°	369.5	23.2
30°-40°	70.0	4.4
40°-50°	8.8	0.6
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1514.4	95.0
0°-40°	1584.4	99.3
0°-60°	1594.5	100.0
0°-90°	1595.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1595.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4934	
5°	4791	432
15°	2553	713
25°	801	370
35°	100	70
45°	10	9
55°	2	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857162

CATALOG NUMBER: LX4C20D010 EU4209035 4LBHYLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4934.1
2.5°	4926.0
5°	4791.2
7.5°	4481.9
10°	4015.6
12.5°	3313.7
15°	2552.9
17.5°	1938.6
20°	1542.3
22.5°	1149.7
25°	800.6
27.5°	492.0
30°	262.9
32.5°	177.5
35°	100.2
37.5°	43.5
40°	25.0
42.5°	16.2
45°	10.3
47.5°	5.9
50°	3.7
52.5°	1.5
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)