

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839965

Luminaire Tested: **LDS4C35D010 EU4359030 4LBSWMH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359030 4LBSWMH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH WMH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3024.0 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839965

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBSWMH

Luminous Intensity Polar Plot





TEST NUMBER: P839965

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBSWMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194293
5°	193395
10°	189406
15°	182526
20°	174117
25°	164739
30°	155392
35°	146317
40°	137761
45°	128412
50°	117103
55°	103410
60°	87545
65°	68721
70°	49067
75°	26866
80°	4740
85°	0



TEST NUMBER: P839965

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBSWMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.1	4.9
10°-20°	402.7	13.3
20°-30°	559.2	18.5
30°-40°	610.2	20.2
40°-50°	569.2	18.8
50°-60°	432.1	14.3
60°-70°	236.6	7.8
70°-80°	65.1	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1110.0	36.7
0°-40°	1720.2	56.9
0°-60°	2721.4	90.0
0°-90°	3024.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3024.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1582	
5°	1568	148
15°	1435	403
25°	1215	559
35°	976	610
45°	739	569
55°	483	432
65°	236	237
75°	57	65
85°	0	1
90°	0	



TEST NUMBER: P839965

CATALOG NUMBER: LDS4C35D010 EU4359030 4LBSWMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1581.5
2.5°	1581.5
5°	1568.2
7.5°	1548.3
10°	1518.3
12.5°	1478.4
15°	1435.1
17.5°	1381.8
20°	1331.8
22.5°	1271.9
25°	1215.3
27.5°	1158.7
30°	1095.4
32.5°	1035.5
35°	975.6
37.5°	915.6
40°	859.0
42.5°	799.1
45°	739.1
47.5°	679.2
50°	612.7
52.5°	549.4
55°	482.8
57.5°	419.5
60°	356.3
62.5°	293.0
65°	236.4
67.5°	183.1
70°	136.6
72.5°	93.2
75°	56.6
77.5°	26.6
80°	6.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)