

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839975

Luminaire Tested: **LDS4C35D010 EU4359035 4LBSWMH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359035 4LBSWMH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH WMH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3067.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839975

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBSWMH

Luminous Intensity Polar Plot





TEST NUMBER: P839975

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBSWMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197057
5°	196145
10°	192101
15°	185121
20°	176601
25°	167070
30°	157605
35°	148387
40°	139718
45°	130254
50°	118766
55°	104888
60°	88774
65°	69709
70°	49749
75°	27246
80°	4811
85°	0



TEST NUMBER: P839975

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBSWMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.2	4.9
10°-20°	408.4	13.3
20°-30°	567.1	18.5
30°-40°	618.9	20.2
40°-50°	577.3	18.8
50°-60°	438.2	14.3
60°-70°	239.9	7.8
70°-80°	66.0	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1125.8	36.7
0°-40°	1744.6	56.9
0°-60°	2760.1	90.0
0°-90°	3067.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3067.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1604	
5°	1590	150
15°	1456	408
25°	1232	567
35°	989	619
45°	750	577
55°	490	438
65°	240	240
75°	57	66
85°	0	1
90°	0	



TEST NUMBER: P839975

CATALOG NUMBER: LDS4C35D010 EU4359035 4LBSWMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1604.0
2.5°	1604.0
5°	1590.5
7.5°	1570.3
10°	1539.9
12.5°	1499.4
15°	1455.5
17.5°	1401.5
20°	1350.8
22.5°	1290.0
25°	1232.5
27.5°	1175.2
30°	1111.0
32.5°	1050.2
35°	989.4
37.5°	928.6
40°	871.2
42.5°	810.4
45°	749.7
47.5°	688.9
50°	621.4
52.5°	557.2
55°	489.7
57.5°	425.5
60°	361.3
62.5°	297.2
65°	239.8
67.5°	185.7
70°	138.5
72.5°	94.6
75°	57.4
77.5°	27.0
80°	6.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)