

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857194

Luminaire Tested: **LX4C20D010 EX4C209040 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P857194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EX4C209040 4LBSLI
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2073.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857194

CATALOG NUMBER: LX4C20D010 EX4C209040 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P857194

CATALOG NUMBER: LX4C20D010 EX4C209040 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181848
5°	177733
10°	166901
15°	155283
20°	144008
25°	131284
30°	116878
35°	103589
40°	93113
45°	83326
50°	71481
55°	57510
60°	42851
65°	27355
70°	13183
75°	2183
80°	1627
85°	0



TEST NUMBER: P857194

CATALOG NUMBER: LX4C20D010 EX4C209040 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.2	6.5
10°-20°	342.3	16.5
20°-30°	443.6	21.4
30°-40°	434.6	21.0
40°-50°	368.4	17.8
50°-60°	241.5	11.6
60°-70°	97.1	4.7
70°-80°	11.1	0.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	920.1	44.4
0°-40°	1354.7	65.3
0°-60°	1964.5	94.8
0°-90°	2073.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2073.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1480	
5°	1441	134
15°	1221	342
25°	968	444
35°	691	435
45°	480	368
55°	268	241
65°	94	97
75°	5	11
85°	0	0
90°	0	



TEST NUMBER: P857194

CATALOG NUMBER: LX4C20D010 EX4C209040 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1480.2
2.5°	1468.7
5°	1441.2
7.5°	1395.2
10°	1337.9
12.5°	1275.9
15°	1220.9
17.5°	1161.2
20°	1101.5
22.5°	1037.3
25°	968.5
27.5°	897.3
30°	823.9
32.5°	755.0
35°	690.7
37.5°	638.0
40°	580.6
42.5°	530.1
45°	479.6
47.5°	426.8
50°	374.0
52.5°	321.3
55°	268.5
57.5°	220.3
60°	174.4
62.5°	133.1
65°	94.1
67.5°	62.0
70°	36.7
72.5°	16.0
75°	4.6
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)